


# BroadBand Light

## MULA K2 BroadBand Light

Filters	ACNE (400-400 & 890-1200nm) VASCULAR (530-450 & 900-1200nm)	Pulse Number	1-3
	420nm (420-950nm) 500nm (500-600nm) 530nm (530-950nm) 530nm (550-650nm) 540nm (540-950nm) 590nm (590-950nm) 615nm (615-950nm) 640nm (640-950nm) 615nm (695-950nm)	Pulse Interval	1-99ms
		Screen	10.1 Inch Industrial Capacitive Touch Screen
		Voltage	AC220V 50Hz
		Power	≤2300W
Spot Size	14*38mm	Cooling System	TEC Electronics Cooling + Water Cooling + Air Cooling
Handpiece	BroadBand Light Handpiece	Working Temperature	15-30 °C
Fluence	2-50J/cm2	Dimension/O.W.	Machine: 810x540x170mm, 28 KG Trolley: 445*510*1000mm, 25KG (Optional)
Frequency	1-5Hz		
Pulse Width	1-30ms		





## One Handpiece, Numerous Treatments


### Freckle Removal Treatment




### Inflammation, Acne Removal Treatment




### Superficial Blood Vessel Removal Treatment



### Wrinkles Removal and Skin Rejuvenation Treatment



## Different Sizes of Finesse Adapter



### Adjustable Window Design in Handpiece

14\*38mm sapphire treatment spot size



### Smart Trolley

Press self-locking storage box  
Press to eject lightly  
Convenient to storage the filters



### Precise Treatment

Pulse number, pulse width, and pulse interval time are adjustable